

HoloPRISM® R-358 METALLIZED PAPER

REVISION DATE: 06/03/10

Product designed for general label pressure sensitive or festive and decorate packaging applications.

R-358

TYPICAL PROPERTIES AND VALUES

PROPERTY	UNITS	AVERAGE	RANGE	TEST METHOD
Basis Weight	lbs/3000 sq. ft.	58	±2.5	T-410 OM-02 TAPPI
	gsm	94	±4.0	
Caliper	mils	3.3	±0.3	T-411 OM-97 TAPPI
	microns	84	±8.0	
Moisture	%	3.6	± 0.7	T-412 OM-02 TAPPI
Elmendorf Tear – MD CD	grams	44	Note 2	T-414 OM-98 TAPPI
	grams	52	Note 2	
Gurley Stiffness – MD CD	mg	105	Note 2	T-543 OM-00 TAPPI
	mg	60	Note 2	
Tensile – MD, Dry CD, Dry	lbs/in	31	Note 2	T-494 OM-01 TAPPI
	kN/meter	5.5	Note 2	
	lbs/in	12	Note 2	
	kN/meter	2.1	Note 2	

NOTES:

- The data above for the VACUMET product are typical values and are not limiting specifications.** Standard test conditions are 72° F, 50% RH unless otherwise noted. The information contained herein represents the best data available to Vacumet, and we believe it is reliable. No statement with respect to use is intended as a recommendation and no warranty is made. We urge purchasers to conduct confirmatory tests for suitability in their specific use.
- These properties are determined by the base paper mill – more detailed data is available upon request.
- The aluminum used in the metallizing process is generally regarded as safe (GRAS) as designated in the 1958 Food Additive Amendments to the Federal Food, Drug and Cosmetic Act.

For any questions, samples or additional information, please contact Customer Service at 1 800.343.6977.